



# Mini 300 Cube DBP300

## ZBP300 CFRM WH

IP WH, White

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

### Product data

General Information			
Accessory color	White	Order code	910990000008
Product family code	ZBP300 [IP WH]	Material Nr. (12NC)	910990000008
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8690653183834
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8690653183834
Product Data			
Order product name	ZBP300 CFRM WH		
Full product name	ZBP300 CFRM WH		
Full product code	869065318383400		