



Broadway SGP268

SGP268 SON-T150W 230V-50Hz GB SI

SON-T, 150 W, 230 V, 50 Hz, Glass bowl/cover, Silver

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Open T-POT
Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Power Consumption	150 W
Mechanical and Housing	
Housing Color	Silver

Approval and Application	
Ingress protection code	IP43/66 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Product Data	
Order product name	SGP268 SON-T150W 230V-50Hz GB SI
Full product name	SGP268 SON-T150W 230V-50Hz GB SI
Full product code	911400329180
Order code	911400329180
Material Nr. (12NC)	911400329180
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Broadway SGP268

Dimensional drawing

