



# Tango MMF283

## MMF283 MHN-TD150W 240V-50Hz S

MHN-TD, 150 W, Symmetrical

Compact, sturdy floodlight complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. All-weather construction designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	MHN-TD
Cap-Base	- [-]
Gear	CONV [Conventional]

  

Light Technical	
Number of light sources	1
Optic type outdoor	Symmetrical

  

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	150 W

  

Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

  

Product Data	
Order product name	MMF283 MHN-TD150W 240V-50Hz S
Full product name	MMF283 MHN-TD150W 240V-50Hz S
Full product code	911400419880
Order code	911400419880
Material Nr. (12NC)	911400419880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Tango MMF283

## Dimensional drawing

