



Tango MMF383

SMF383 SON-T400W 240V-50Hz

SON-T, 400 W

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optic type outdoor	-
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	400 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	SMF383 SON-T400W 240V-50Hz
Full product name	SMF383 SON-T400W 240V-50Hz
Full product code	911400433980
Order code	911400433980
Material Nr. (12NC)	911400433980
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Tango MMF383

Dimensional drawing

