



TCS398 C

TCS398 C 2xTL-D36W HFE M6

2, MASTER TL-D, 36 W, HF Standard, Matt optic double parabolic louver closed

TCS398 is also suitable for TL5 or TLD fluorescent lamps, with a wide range of high-performance optics. The luminaire is a direct version and can be surface-mounted or suspended. Two types of suspension systems are available: wire and tube suspension. The luminaire can be mounted individually and in configurations.


Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFE [HF Standard]
Light Technical	
Number of light sources	2
Light source color	-
Optic type	Matt optic double parabolic louver closed
Operating and Electrical	
Power Consumption	36 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Order product name	TCS398 C 2xTL-D36W HFE M6
Full product name	TCS398 C 2xTL-D36W HFE M6
Full product code	911400633580
Order code	911400633580
Material Nr. (12NC)	911400633580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

TCS398 C

Dimensional drawing



Product	A	B	C
TCS398 C 2xTL-D36W HFE M6	1,240 mm	1,310 mm	195 mm

