



Latina FBH020/022 C

FBH022 2xPL-C/2P 18W I WH

2, MASTER PL-C 2 Pin, 18 W, White

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. It is available in square and round models. Latina comes in ready-to-install kit versions with pre-mounted lamps and preconnected separate gear box. The accessories include a frosted glass and clear decorative glass cover.

Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	2
Operating and Electrical	
Power Consumption	18 W
Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Order product name	FBH022 2xPL-C/2P 18W I WH
Full product name	FBH022 2xPL-C/2P 18W I WH
Full product code	911400804680
Order code	911400804680
Material Nr. (12NC)	911400804680
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163181271
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163181271

Latina FBH020/022 C

Dimensional drawing

