



# Latina FBH020/022 C

## FBH022 C 2xPL-C/4P26W EB GR

2, MASTER PL-C 4 Pin, 26 W, Electronic, Grey

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. It is available in square and round models. Latina comes in ready-to-install kit versions with pre-mounted lamps and preconnected separate gear box. The accessories include a frosted glass and clear decorative glass cover.

### Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Operating and Electrical	
Power Consumption	26 W
Mechanical and Housing	
Housing Color	Grey

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FBH022 C 2xPL-C/4P26W EB GR
Full product name	FBH022 C 2xPL-C/4P26W EB GR
Full product code	911400805580
Order code	911400805580
Material Nr. (12NC)	911400805580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Latina FBH020/022 C

Dimensional drawing

