



# Fugato Adjustable

## MBS254 C 1xCDM-TC35W EB 24 WH

1, MASTERColour CDM-TC, 35 W, Electronic, Beam angle 24°

Comprising both fixed and adjustable downlights, the Fugato conventional range provides exceptional freedom in terms of lighting design. Furthermore, Fugato's adjustable luminaires offer a choice of models with cardanic suspension or full internal/external adjustability. The flexibility that this allows, combined with the extensive selection of optics (including, for some models, an innovative dual-optic), ensures maximum design freedom. At the same time, visual consistency is assured, as the adjustable versions have the same dimensions and family look as the fixed models. The Fugato downlights come in five different sizes (for 95, 125, 175, 225 and 275 mm cut-outs). Fixed Fugato downlights accommodate compact fluorescent lamps, high-intensity discharge lamps and halogen lamps, while the adjustable and cardanic versions take high-intensity discharge and halogen lamps. A breakthrough feature of the optics is the 'dual-optic concept', where the metal top reflector is combined with a metallised polymer lower optic. A dual-optic offers several significant advantages over a single polymer optic – improved heat dissipation, straightforward integration of functional and architectural accessories, and a choice of high-gloss, matt or white finishes. The Fugato downlights come in five sizes based on the optimum combination of light output, efficiency and glare rating, making them an ideal replacement for other – larger and squarer – office luminaires. Our leading-edge optics provide excellent light output and effective glare shielding (in accordance with CIE EN12464-1), resulting in a highly efficient lighting performance. State-of-the-art electronic gear versions are also available, yielding further significant energy savings. Based on the optimum combination of light output, efficiency and glare rating, Fugato represents a genuine alternative to other – larger and squarer – luminaires. A wide choice of accessories, optic finishes and integrated lighting controls ensure a comfortable lighting ambience.

### Product data

# Fugato Adjustable

## General Information

Lamp family code	CDM-TC [MASTERColour CDM-TC]
Gear	EB [Electronic]

## Light Technical

Number of light sources	1
Optic type	Beam angle 24°

## Operating and Electrical

Power Consumption	35 W
-------------------	------

## Mechanical and Housing

Housing Color	White
---------------	-------

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

## Product Data

Order product name	MBS254 C 1xCDM-TC35W EB 24 WH
Full product name	MBS254 C 1xCDM-TC35W EB 24 WH
Full product code	911400807780
Order code	911400807780
Material Nr. (12NC)	911400807780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

