



Fugato Adjustable

MBS254 C 1xCDM-TC70W EB 36 WH

1 pc - MASTERColour CDM-TC - 70 W - Electronic - Beam angle 36°

Comprising both fixed and adjustable downlights, the Fugato conventional range provides exceptional freedom in terms of lighting design. Furthermore, Fugato's adjustable luminaires offer a choice of models with cardanic suspension or full internal/external adjustability. The flexibility that this allows, combined with the extensive selection of optics (including, for some models, an innovative dual-optic), ensures maximum design freedom. At the same time, visual consistency is assured, as the adjustable versions have the same dimensions and family look as the fixed models. The Fugato downlights come in five different sizes (for 95, 125, 175, 225 and 275 mm cut-outs). Fixed Fugato downlights accommodate compact fluorescent lamps, high-intensity discharge lamps and halogen lamps, while the adjustable and cardanic versions take high-intensity discharge and halogen lamps. A breakthrough feature of the optics is the 'dual-optic concept', where the metal top reflector is combined with a metallised polymer lower optic. A dual-optic offers several significant advantages over a single polymer optic – improved heat dissipation, straightforward integration of functional and architectural accessories, and a choice of high-gloss, matt or white finishes. The Fugato downlights come in five sizes based on the optimum combination of light output, efficiency and glare rating, making them an ideal replacement for other – larger and squarer – office luminaires. Our leading-edge optics provide excellent light output and effective glare shielding (in accordance with CIE EN12464-1), resulting in a highly efficient lighting performance. State-of-the-art electronic gear versions are also available, yielding further significant energy savings. Based on the optimum combination of light output, efficiency and glare rating, Fugato represents a genuine alternative to other – larger and squarer – luminaires. A wide choice of accessories, optic finishes and integrated lighting controls ensure a comfortable lighting ambience.

Данные о продукции

Fugato Adjustable


Общая информация	
Код-дубликат	C [China]
Количество источников света	1 [1 pc]
Код лампового семейства	CDM-TC [MASTERColour CDM-TC]
Мощность лампы	70 W
ПРА	EB [Electronic]
Тип оптики	36 [Beam angle 36°]
Версия для страны	NO [Norway]

Соответствие требованиям и область применения	
Код защиты от проникновения	IP20 [Защита пальцев]

Данные об изделии


Полный код продукта	911400808080
Название продукта для заказа	MBS254 C 1xCDM-TC70W EB 36 WH
Код заказа	00808080
Нумератор — количество на упаковку	1
Нумератор— упаковок на внешний короб	1
Материал № (12NC)	911400808080
Вес нетто (шт.)	0.799 kg

Чертеж размеров




Fugato MBS254 C

Фотометрические данные



IFAS1_MBS254 C 1xCDM-TC70W EB 36.EPS



IFCC1_MBS254 C 1xCDM-TC70W EB 36.EPS

Fugato Adjustable

