



## Fugato Adjustable

**MBS252 C 1xCDM-TC70W EB 36 WH**

China - 1 pc - MASTERColour CDM-TC - 70 W - Electronic - Beam angle 36° - White

Comprising both fixed and adjustable downlights, the Fugato conventional range provides exceptional freedom in terms of lighting design. Furthermore, Fugato's adjustable luminaires offer a choice of models with cardanic suspension or full internal/external adjustability. The flexibility that this allows, combined with the extensive selection of optics (including, for some models, an innovative dual-optic), ensures maximum design freedom. At the same time, visual consistency is assured, as the adjustable versions have the same dimensions and family look as the fixed models. The Fugato downlights come in five different sizes (for 95, 125, 175, 225 and 275 mm cut-outs). Fixed Fugato downlights accommodate compact fluorescent lamps, high-intensity discharge lamps and halogen lamps, while the adjustable and cardanic versions take high-intensity discharge and halogen lamps. A breakthrough feature of the optics is the 'dual-optic concept', where the metal top reflector is combined with a metallised polymer lower optic. A dual-optic offers several significant advantages over a single polymer optic – improved heat dissipation, straightforward integration of functional and architectural accessories, and a choice of high-gloss, matt or white finishes. The Fugato downlights come in five sizes based on the optimum combination of light output, efficiency and glare rating, making them an ideal replacement for other – larger and squarer – office luminaires. Our leading-edge optics provide excellent light output and effective glare shielding (in accordance with CIE EN12464-1), resulting in a highly efficient lighting performance. State-of-the-art electronic gear versions are also available, yielding further significant energy savings. Based on the optimum combination of light output, efficiency and glare rating, Fugato represents a genuine alternative to other – larger and squarer – luminaires. A wide choice of accessories, optic finishes and integrated lighting controls ensure a comfortable lighting ambience.


### Product data

Fugato Adjustable

General Information	
Duplication code	C [ China]
Number of light sources	1 [ 1 pc]
Lamp family code	CDM-TC [ MASTERColour CDM-TC]
Lamp power	70 W
Gear	EB [ Electronic]
Optic type	36 [ Beam angle 36°]
Country version	NO [ Norway]
Approval and Application	
Ingress protection code	IP20 [ Finger-protected]


Product Data	
Full product code	911400808780
Order product name	MBS252 C 1xCDM-TC70W EB 36 WH
Order code	911400808780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911400808780
Net Weight (Piece)	0.719 kg

Dimensional drawing




Fugato MBS252 C

Photometric data



IFAS1\_MBS252 C 1xCDM-TC70W EB 36.EPS



IFCC1\_MBS252 C 1xCDM-TC70W EB 36.EPS

## Fugato Adjustable

