



Fugato Fixed

MBS250 C 1xCDM-TC70W EB 36 WH

1, MASTERColour CDM-TC, 70 W, Electronic, Beam angle 36°, White

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Product data

General Information	
Lamp family code	CDM-TC [MASTERColour CDM-TC]
Gear	EB [Electronic]
Light Technical	
Number of light sources	1
Optic type	Beam angle 36°
Operating and Electrical	
Power Consumption	70 W
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	MBS250 C 1xCDM-TC70W EB 36 WH
Full product name	MBS250 C 1xCDM-TC70W EB 36 WH
Full product code	911400809080
Order code	911400809080
Material Nr. (12NC)	911400809080
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Fugato Fixed

Dimensional drawing

