



Fugato Fixed

MBS250 C 1xCDM-TC70W EB 36 WH

China - 1 pc - MASTERColour CDM-TC - 70 W - Electronic - Beam angle 36° - White

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Данные о продукции

Общая информация	
Код-дубликат	C [China]
Количество источников света	1 [1 pc]
Код лампового семейства	CDM-TC [MASTERColour CDM-TC]
Мощность лампы	70 W
ПРА	EB [Electronic]
Тип оптики	36 [Beam angle 36°]


Соответствие требованиям и область применения

Код защиты от проникновения	IP20 [Защита пальцев]
-----------------------------	------------------------

Данные об изделии	
Полный код продукта	911400809080
Название продукта для заказа	MBS250 C 1xCDM-TC70W EB 36 WH
Код заказа	00809080
Нумератор — количество на упаковку	1
Нумератор — упаковок на внешний короб	1
Материал № (12NC)	911400809080
Вес нетто (шт.)	0.799 kg

Fugato Fixed

Чертеж размеров



Fugato MBS250 C

