



Latina FBH020/022 C

FBH022 2xPL-C/4P 26W NG WH

2, MASTER PL-C 4 Pin, 26 W, White

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. It is available in square and round models. Latina comes in ready-to-install kit versions with pre-mounted lamps and preconnected separate gear box. The accessories include a frosted glass and clear decorative glass cover.

Product data

| General Information | |
|--------------------------|-----------------------------|
| Lamp family code | PL-C/4P [MASTER PL-C 4 Pin] |
| Light Technical | |
| Number of light sources | 2 |
| Operating and Electrical | |
| Power Consumption | 26 W |
| Mechanical and Housing | |
| Housing Color | White |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |

| Product Data | |
|---------------------------------|----------------------------|
| Order product name | FBH022 2xPL-C/4P 26W NG WH |
| Full product name | FBH022 2xPL-C/4P 26W NG WH |
| Full product code | 911400812080 |
| Order code | 911400812080 |
| Material Nr. (12NC) | 911400812080 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 4 |

Latina FBH020/022 C

Dimensional drawing

