



# Fugato Fixed

## MBS260 C 1xCDM-T70W IC 60 WH

1, MASTERColour CDM-T, 70 W, Beam angle 60°, White

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

### Product data

| General Information      |                            |
|--------------------------|----------------------------|
| Lamp family code         | CDM-T [MASTERColour CDM-T] |
| Gear                     | CONV [Conventional]        |
| Light Technical          |                            |
| Number of light sources  | 1                          |
| Optic type               | Beam angle 60°             |
| Operating and Electrical |                            |
| Power Consumption        | 70 W                       |
| Mechanical and Housing   |                            |
| Housing Color            | White                      |

| Approval and Application        |                              |
|---------------------------------|------------------------------|
| Ingress protection code         | IP20 [Finger-protected]      |
| Product Data                    |                              |
| Order product name              | MBS260 C 1xCDM-T70W IC 60 WH |
| Full product name               | MBS260 C 1xCDM-T70W IC 60 WH |
| Full product code               | 911400816880                 |
| Order code                      | 911400816880                 |
| Material Nr. (12NC)             | 911400816880                 |
| Numerator - Quantity Per Pack   | 1                            |
| Numerator - Packs per outer box | 1                            |

Fugato Fixed

Dimensional drawing

