



# Fugato Fixed

## MBS260 C 1xCDM-T150W IC 36 WH

China - 1 pc - MASTERColour CDM-T - 150 W - Inductive parallel compensated - Beam angle 36° - White

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

### Product data

General Information	
Duplication code	C [ China]
Number of light sources	1 [ 1 pc]
Lamp family code	CDM-T [ MASTERColour CDM-T]
Lamp power	150 W
Compensation circuit	Inductive parallel compensated
Gear	CONV [ Conventional]
Optic type	36 [ Beam angle 36°]


### Approval and Application

Ingress protection code	IP20 [ Finger-protected]
-------------------------	--------------------------

Product Data	
Full product code	911400817080
Order product name	MBS260 C 1xCDM-T150W IC 36 WH
Order code	911400817080
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911400817080
Net Weight (Piece)	3.233 kg

Fugato Fixed

Dimensional drawing



Fugato MBS260 C

