



Fugato Fixed

FBS261 C 2xPL-C/4P18W HFP C WH

China - 2 pcs - MASTER PL-C 4 Pin - 18 W - Electronic Primalume - High-gloss mirror - White

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.


Product data

General Information	
Duplication code	C [China]
Number of light sources	2 [2 pcs]
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Lamp power	18 W
Compensation circuit	-
Gear	EBP [Electronic Primalume]
Optic type	C [High-gloss mirror]
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Full product code	911400820880
Order product name	FBS261 C 2xPL-C/4P18W HFP C WH
Order code	911400820880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911400820880
Net Weight (Piece)	1.305 kg

Fugato Fixed

Dimensional drawing



FBS261 C

