



Fugato Fixed

FBS261 C 2xPL-C/4P18W HFP C WH

2, MASTER PL-C 4 Pin, 18 W, Electronic Primalume, High-gloss mirror, White

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	EBP [Electronic Primalume]
Light Technical	
Number of light sources	2
Optic type	High-gloss mirror
Operating and Electrical	
Power Consumption	18 W
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FBS261 C 2xPL-C/4P18W HFP C WH
Full product name	FBS261 C 2xPL-C/4P18W HFP C WH
Full product code	911400820880
Order code	911400820880
Material Nr. (12NC)	911400820880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Fugato Fixed

Dimensional drawing

