



FBH/FBS145 C

MBS145 C 1xCDM-TD70W IC WH

1, MASTERColour CDM-TD, 70 W, White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

Product data

General Information	
Lamp family code	CDM-TD [MASTERColour CDM-TD]
Cap-Base	- [-]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	-
Operating and Electrical	
Power Consumption	70 W
Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	MBS145 C 1xCDM-TD70W IC WH
Full product name	MBS145 C 1xCDM-TD70W IC WH
Full product code	911400829480
Order code	00829480
Material Nr. (12NC)	911400829480
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

FBH/FBS145 C

Dimensional drawing

