



FBH/FBS145 C

MBS145 C 1xCDM-T70W IC WH

1, MASTERColour CDM-T, 70 W, White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

Product data

| General Information | |
|-------------------------------|----------------------------|
| Lamp family code | CDM-T [MASTERColour CDM-T] |
| Cap-Base | - [-] |
| Gear | CONV [Conventional] |
| Light Technical | |
| Number of light sources | 1 |
| Optical cover type | - |
| Operating and Electrical | |
| Power Consumption | 70 W |
| Controls and Dimming | |
| Driver/power unit/transformer | - |
| Mechanical and Housing | |
| Housing Color | White |

| Approval and Application | |
|---------------------------------|---------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Product Data | |
| Order product name | MBS145 C 1xCDM-T70W IC WH |
| Full product name | MBS145 C 1xCDM-T70W IC WH |
| Full product code | 911400829680 |
| Order code | 911400829680 |
| Material Nr. (12NC) | 911400829680 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

FBH/FBS145 C

Dimensional drawing

