



# FBH/FBS145 C

## MBS145 C 1xCDM-T150W IC WH

1, MASTERColour CDM-T, 150 W, White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

### Product data

General Information	
Lamp family code	CDM-T [MASTERColour CDM-T]
Cap-Base	- [-]
Gear	CONV [Conventional]

  

Light Technical	
Number of light sources	1
Optical cover type	-

  

Operating and Electrical	
Power Consumption	150 W

  

Controls and Dimming	
Driver/power unit/transformer	-

  

Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

  

Product Data	
Order product name	MBS145 C 1xCDM-T150W IC WH
Full product name	MBS145 C 1xCDM-T150W IC WH
Full product code	911400829780
Order code	911400829780
Material Nr. (12NC)	911400829780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# FBH/FBS145 C

## Dimensional drawing

