



# FBH/FBS145 C

## FBS145 C 1xPL-C/2P18W IC FG WH

1, MASTER PL-C 2 Pin, 18 W, Flat glass, White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

### Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Cap-Base	- [-]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	Flat glass
Operating and Electrical	
Power Consumption	18 W
Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FBS145 C 1xPL-C/2P18W IC FG WH
Full product name	FBS145 C 1xPL-C/2P18W IC FG WH
Full product code	911400830280
Order code	911400830280
Material Nr. (12NC)	911400830280
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## FBH/FBS145 C

### Dimensional drawing

