



# FBH/FBS145 C

## MBS145 C 1xCDM-T35W IC WH

1, MASTERColour CDM-T, 35 W, White

Professional standard recessed downlights with a 145mm internal diameter.  
Complete with a very efficient highly polished reflector in silver aluminium finish.  
Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

### Product data

General Information	
Lamp family code	CDM-T [MASTERColour CDM-T]
Cap-Base	- [-]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	-
Operating and Electrical	
Power Consumption	35 W
Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	MBS145 C 1xCDM-T35W IC WH
Full product name	MBS145 C 1xCDM-T35W IC WH
Full product code	911400830480
Order code	00830480
Material Nr. (12NC)	911400830480
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291994923
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291994923

## FBH/FBS145 C

### Dimensional drawing

