



# FBH/FBS145 C

## MBS145 C 1xCDM-T35W IC WH

China - 1 pc - MASTERColour CDM-T - 35 W - Inductive parallel compensated - White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.


### Product data

General Information	
Duplication code	C [ China]
Number of light sources	1 [ 1 pc]
Lamp family code	CDM-T [ MASTERColour CDM-T]
Lamp power	35 W
Cap base	- [ -]
Compensation circuit	Inductive parallel compensated
Gear	CONV [ Conventional]
Driver/power unit/transformer	No [ -]
Optical cover/lens type	No [ -]
Country version	NO [ Norway]
Operating and Electrical	
Maximum lamp power	No [ -]

Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Product Data	
Full product code	911400830480
Order product name	MBS145 C 1xCDM-T35W IC WH
EAN/UPC – product	8718291994923
Order code	911400830480
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911400830480
Net weight (piece)	2.999 kg



FBH/FBS145 C

Dimensional drawing




FBS145 C

Photometric data



IFAS1\_MBS145 C 1xCDM-T35W.EPS

IFCC1\_MBS145 C 1xCDM-T35W.EPS



IFGU1\_MBS145 C 1xCDM-T35W.EPS

