



# MCS/QCS145 C

## FCS145 C 1xPL-C/2P26W IC WH

1, MASTER PL-C 2 Pin, 26 W, White

Professional surface mounted downlights complimenting the family of the 145 range. Complete with a very efficient highly-polished reflector in silver aluminium finish. Suitable for PAR reflector halogen, the range comes with a standard white decorative plastic ring. Accessories are common and interchangeable for the entire 145 range. Colour options upon request.

### Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Operating and Electrical	
Power Consumption	26 W
Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FCS145 C 1xPL-C/2P26W IC WH
Full product name	FCS145 C 1xPL-C/2P26W IC WH
Full product code	911400832180
Order code	911400832180
Material Nr. (12NC)	911400832180
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## MCS/QCS145 C

### Dimensional drawing

