



MCS/QCS145 C

FCS145 C 2xPL-C/2P26W IC WH

2, MASTER PL-C 2 Pin, 26 W, White

Professional surface mounted downlights complimenting the family of the 145 range. Complete with a very efficient highly-polished reflector in silver aluminium finish. Suitable for PAR reflector halogen, the range comes with a standard white decorative plastic ring. Accessories are common and interchangeable for the entire 145 range. Colour options upon request.

Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	2
Operating and Electrical	
Power Consumption	26 W
Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FCS145 C 2xPL-C/2P26W IC WH
Full product name	FCS145 C 2xPL-C/2P26W IC WH
Full product code	911400832380
Order code	911400832380
Material Nr. (12NC)	911400832380
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291994947
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291994947

MCS/QCS145 C

Dimensional drawing

