



TCH086

TCH085 TL5-28W/840 EI 220-240V ALU

TL5, 28 W, 840 neutral white, Electronic Included, 220 to 240 V, Aluminum

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EI [Electronic Included]
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	28 W
Mechanical and Housing	
Housing Color	Aluminum

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Product Data	
Full product code	911400868180
Order product name	TCH085 TL5-28W/840 EI 220-240V ALU
Order code	911400868180
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	911400868180
Full product name	TCH085 TL5-28W/840 EI 220-240V ALU
EAN/UPC - Case	8710163288475
EAN/UPC - Product/Case	8710163288413

TCH086

Dimensional drawing

