



# TCH086

## TCH084 TL5-28W/840 HF 220-240V

TL5, 28 W, 840 neutral white, Electronic high-frequency, 220 to 240 V

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes
Light Technical	
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	28 W

Product Data	
Full product code	911400874580
Order product name	TCH084 TL5-28W/840 HF 220-240V
Order code	911400874580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	911400874580
Full product name	TCH084 TL5-28W/840 HF 220-240V
EAN/UPC - Case	8710163288857
EAN/UPC - Product/Case	8710163288604

**TCH086**

**Dimensional drawing**

