



TCH086

TCH084 TL5-28W/840 HF 220-240V

TL5, 28 В, Нейтральный белый 840, Электронный высокочастотный, От 220 до 240 Вт

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Данные о продукции

Общая информация	
Код лампового семейства	TL5 [TL5]
ПРА	HF [Электронный высокочастотный]
Технические характеристики освещения	
Цвет источника света	Нейтральный белый 840
Эксплуатационные и электрические характеристики	
Входное напряжение	От 220 до 240 Вт
Энергопотребление	28 В
Данные об изделии	
Название продукта для заказа	TCH084 TL5-28W/840 HF 220-240V

Полное название продукта	TCH084 TL5-28W/840 HF 220-240V
Полный код продукта	911400874580
Код заказа	911400874580
Материал № (12NC)	911400874580
Нумератор — количество на упаковку	1
EAN/UPC — продукт/короб	8710163288604
Нумератор — упаковок на внешний короб	24
EAN/UPC — короб	8710163288857

TCH086

Чертеж размеров

