



TCH086

TCH086 TL5-21W/830 HF 220V TW

TL5, 21 W, 830 warm white, Electronic high-frequency, 220 V

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes
Light Technical	
Number of light sources	1
Light source color	830 warm white
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 to 60 Hz
Power Consumption	21 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class II
Product Data	
Full product code	911400879380
Order product name	TCH086 TL5-21W/830 HF 220V TW
Order code	911400879380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	911400879380
Full product name	TCH086 TL5-21W/830 HF 220V TW
EAN/UPC - Case	8710163289618
EAN/UPC - Product/Case	8710163289496

TCH086

Dimensional drawing

