



# TCH086

## TCH086 TL5-28W/865 HF 220V TW

TL5, 28 W, 865 cool daylight, Electronic high-frequency, 220 V

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes

  

Light Technical	
Number of light sources	1
Light source color	865 cool daylight

  

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 to 60 Hz
Power Consumption	28 W

  

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class II
----------------------	-----------------

  

Product Data	
Full product code	911400879880
Order product name	TCH086 TL5-28W/865 HF 220V TW
Order code	911400879880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	911400879880
Full product name	TCH086 TL5-28W/865 HF 220V TW
EAN/UPC - Case	8710163289649
EAN/UPC - Product/Case	8710163289526

# TCH086

## Dimensional drawing

