



# Basic Spot MRS070

LRS070 1x MAX50W/12V-GU5.3 L300 GR

1, GU5.3, Grey

The affordable Smart Spot projector range is a reliable and flexible solution offering a choice of CDM and halogen lamps in various shapes and colors. Designed for operation in conjunction with the Smart Track family, it can be track-mounted or fixed on the ceiling. Smart Spot delivers a good accent lighting effect, making it suitable for projector applications in shops or art galleries. Its stylish design is ideal for integration in a fashion environment and ambience.

## Product data

<b>General Information</b>		<b>Full product name</b>	LRS070 1x MAX50W/12V-GU5.3 L300 GR
Cap-Base	GU5.3 [GU5.3]	Full product code	911400896080
Gear	-	Order code	911400896080
<b>Light Technical</b>		Material Nr. (12NC)	911400896080
Number of light sources	1	Numerator - Quantity Per Pack	1
<b>Mechanical and Housing</b>		EAN/UPC - Product/Case	6923828688677
Housing Color	Grey	Numerator - Packs per outer box	10
<b>Product Data</b>		EAN/UPC - Case	6923828601416
Order product name	LRS070 1x MAX50W/12V-GU5.3 L300 GR		

## Basic Spot MRS070

### Dimensional drawing

