



# Basic Spot MRS070

LCS070 1x MAX50W/12V-GU5.3 L300 BK

1, GU5.3, Black

The affordable Smart Spot projector range is a reliable and flexible solution offering a choice of CDM and halogen lamps in various shapes and colors. Designed for operation in conjunction with the Smart Track family, it can be track-mounted or fixed on the ceiling. Smart Spot delivers a good accent lighting effect, making it suitable for projector applications in shops or art galleries. Its stylish design is ideal for integration in a fashion environment and ambience.

## Product data

|                               |                                    |                                 |                                    |
|-------------------------------|------------------------------------|---------------------------------|------------------------------------|
| <b>General Information</b>    |                                    | <b>Full product name</b>        | LCS070 1x MAX50W/12V-GU5.3 L300 BK |
| Cap-Base                      | GU5.3 [GU5.3]                      | Full product code               | 911400896880                       |
| Gear                          | -                                  | Order code                      | 911400896880                       |
| <b>Light Technical</b>        |                                    | Material Nr. (12NC)             | 911400896880                       |
| Number of light sources       | 1                                  | Numerator - Quantity Per Pack   | 1                                  |
| <b>Mechanical and Housing</b> |                                    | EAN/UPC - Product/Case          | 6923828688752                      |
| Housing Color                 | Black                              | Numerator - Packs per outer box | 10                                 |
| <b>Product Data</b>           |                                    | EAN/UPC - Case                  | 6923828601492                      |
| Order product name            | LCS070 1x MAX50W/12V-GU5.3 L300 BK |                                 |                                    |

## Basic Spot MRS070

### Dimensional drawing

