



# Broadway SGP268

## SGP268 SON-T250W 220V-50Hz GB ALU

SON-T, 250 W, 220 V, 50 Hz, Glass bowl/cover, Aluminum

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

### Product data

| General Information      |                  |
|--------------------------|------------------|
| Lamp family code         | SON-T [SON-T]    |
| Cap-Base                 | E40 [E40]        |
| Gear                     | SGR [SON gear]   |
| Light Technical          |                  |
| Number of light sources  | 1                |
| Optical cover type       | Glass bowl/cover |
| Optic type outdoor       | Open T-POT       |
| Operating and Electrical |                  |
| Input Voltage            | 220 V            |
| Line Frequency           | 50 Hz            |
| Power Consumption        | 250 W            |
| Mechanical and Housing   |                  |
| Housing Color            | Aluminum         |

| Approval and Application        |   |
|---------------------------------|---|
| Ingress protection code         | IP43/66 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof] |
| Product Data                    |   |
| Order product name              | SGP268 SON-T250W 220V-50Hz GB ALU   |
| Full product name               | SGP268 SON-T250W 220V-50Hz GB ALU   |
| Full product code               | 911400988780  |
| Order code                      | 00988780  |
| Material Nr. (12NC)             | 911400988780  |
| Numerator - Quantity Per Pack   | 1   |
| Numerator - Packs per outer box | 1   |

## Broadway SGP268

### Dimensional drawing

