



# Broadway SGP268

## SGP268 SON-T250W 220V-50Hz GB ALU

SON-T, 250 W, 220 V, 50 Hz, Glass bowl/cover, Aluminum

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]

  

Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Open T-POT

  

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	250 W

  

Mechanical and Housing	
Housing Color	Aluminum

Approval and Application	
Ingress protection code	IP43/66 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]

  

Product Data	
Order product name	SGP268 SON-T250W 220V-50Hz GB ALU
Full product name	SGP268 SON-T250W 220V-50Hz GB ALU
Full product code	911400988780
Order code	911400988780
Material Nr. (12NC)	911400988780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Broadway SGP268

## Dimensional drawing

