



# Velocity

## SGP338 SON-T400W 220V-50Hz GB RAL7040

SON-T, 400 W, 220 V, 50 Hz, Glass bowl/cover

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]

  

Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover

  

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	400 W

Approval and Application	
Ingress protection code	IP43/66 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]

  

Product Data	
Order product name	SGP338 SON-T400W 220V-50Hz GB RAL7040
Full product name	SGP338 SON-T400W 220V-50Hz GB RAL7040
Full product code	911400997780
Order code	911400997780
Material Nr. (12NC)	911400997780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Velocity

### Dimensional drawing

