



Velocity

SGP338 SON-T250W 240V-50Hz GB RAL7040

SON-T, 250 W, 240 V, 50 Hz, Glass bowl/cover

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	250 W
Approval and Application	
Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]

Product Data	
Order product name	SGP338 SON-T250W 240V-50Hz GB RAL7040
Full product name	SGP338 SON-T250W 240V-50Hz GB RAL7040
Full product code	911400998180
Order code	911400998180
Material Nr. (12NC)	911400998180
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Velocity

Dimensional drawing

