



Savio TCS760/762 C

TCS760 C 4xTL5-14W HFP AC-MLO FU

4, TL5, 14 W, HF Performer, Acrylate micro-lens optic, Fuse included

Featuring Philips' patented micro-lens optic technology, Savio is a complete luminaire range that offers the ideal combination of stylish design and optimum performance for both task and general lighting. Savio has an edge-to-edge lighting appearance with a uniform and comfortable brightness impression – a real 'surface of light'. The micro-lens optic consists of a single plate and is embedded in a housing made of high-quality natural anodized aluminum. Savio ensures optimum light distribution and full glare control in compliance with the latest office-lighting norm (EN 12464-1). Savio luminaires with Dynamic Lighting keep us feeling active by creating dynamic artificial light that varies over the course of the day or is set according to personal preference. Savio is available as suspended and surface-mounted.

Product data

General Information		Power Consumption	
Lamp family code	TL5 [TL5]	14 W	
Gear	HFP [HF Performer]	Approval and Application	
Flammability mark	For mounting on normally flammable surfaces	Ingress protection code	IP40 [Wire-protected]
Light Technical		Mech. impact protection code	IK03 [0.3 J]
Number of light sources	4	Protection class IEC	Safety class I
Optical cover type	Acrylate micro-lens optic	Product Data	
Operating and Electrical		Order product name	TCS760 C 4xTL5-14W HFP AC-MLO FU
Input Voltage	220 to 240 V	Full product name	TCS760 C 4xTL5-14W HFP AC-MLO FU
Line Frequency	50 to 60 Hz	Full product code	911401005780
		Order code	911401005780

Savio TCS760/762 C

Material Nr. (12NC)	911401005780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

