



Savio TPS760 C

TPS760 C 2xTL5-35W HFP AC-MLO FU SMS

2, TL5, 35 W, HF Performer, Acrylate micro-lens optic

Featuring Philips' patented micro-lens optic technology, Savio is a complete luminaire range that offers the ideal combination of stylish design and optimum performance for both task and general lighting. Savio has an edge-to-edge lighting appearance with a uniform and comfortable brightness impression – a real 'surface of light'. The micro-lens optic consists of a single plate and is embedded in a housing made of high-quality natural anodized aluminum. Savio ensures optimum light distribution and full glare control in compliance with the latest office-lighting norm (EN 12464-1). Savio luminaires with Dynamic Lighting keep us feeling active by creating dynamic artificial light that varies over the course of the day or is set according to personal preference. Savio is available as suspended and surface-mounted.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Flammability mark	For mounting on normally flammable surfaces

Light Technical	
Number of light sources	2
Optical cover type	Acrylate micro-lens optic

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	35 W

Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Product Data	
Order product name	TPS760 C 2xTL5-35W HFP AC-MLO FU SMS
Full product name	TPS760 C 2xTL5-35W HFP AC-MLO FU SMS
Full product code	911401005980
Order code	911401005980
Material Nr. (12NC)	911401005980
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Savio TPS760 C

Dimensional drawing

