



Celino TCS680 C

TCS680 C 2xTL5-28W HFP AC-MLO FU ALU

2, TL5, 28 W, HF Performer, Acrylate micro-lens optic, Fuse included, Aluminum

Celino is a complete luminaire range that reflects the market trend towards miniaturization and architectural integration, while at the same time delivering a significant advance in optical performance. Celino features Philips' aluminum micro optic with 3D lamellae, which ensures optimum visual comfort and efficiency in compliance with the latest office-lighting norm (EN 12464-1). Made of natural anodized aluminum, the housing of Celino is a mere 71 mm wide and has die-cast-aluminum end caps. The design allows multiple luminaires to be connected in a line arrangement. Celino is available as a full range – suspended, surface-mounted, free-standing and wall-mounted – for maximum freedom in application.

Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	Aluminum
Gear	HFP [HF Performer]	Approval and Application	
Light Technical		Ingress protection code	IP20 [Finger-protected]
Number of light sources	2	Protection class IEC	Safety class I
Optic type	-	Product Data	
Optical cover type	Acrylate micro-lens optic	Order product name	TCS680 C 2xTL5-28W HFP AC-MLO FU ALU
Operating and Electrical		Full product name	TCS680 C 2xTL5-28W HFP AC-MLO FU ALU
Power Consumption	28 W	Full product code	911401015180
		Order code	911401015180
		Material Nr. (12NC)	911401015180
		Numerator - Quantity Per Pack	1

Celino TCS680 C

Numerator - Packs per outer box	1
---------------------------------	---

Dimensional drawing

