



Arano TCS640 C

TCS640 C 2xTL5-28W HFP D8 FU ALU

2, TL5, 28 W, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Fuse included, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Light Technical	
Number of light sources	2
Optic type	Semi-high-gloss optic 3D micro-lamellae
Optical cover type	-
Operating and Electrical	
Power Consumption	28 W
Mechanical and Housing	
Housing Color	Aluminum

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Product Data	
Order product name	TCS640 C 2xTL5-28W HFP D8 FU ALU
Full product name	TCS640 C 2xTL5-28W HFP D8 FU ALU
Full product code	911401015480
Order code	911401015480
Material Nr. (12NC)	911401015480
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Arano TCS640 C

Dimensional drawing

