



# Arano TCS640 C

## TCS640 C 2xTL5-28W HFP AC-MLO FU ALU

2, TL5, 28 W, HF Performer, Acrylate micro-lens optic, Fuse included, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

### Product data

| General Information      |                           |
|--------------------------|---------------------------|
| Lamp family code         | TL5 [TL5]                 |
| Gear                     | HFP [HF Performer]        |
| Light Technical          |                           |
| Number of light sources  | 2                         |
| Optic type               | -                         |
| Optical cover type       | Acrylate micro-lens optic |
| Operating and Electrical |                           |
| Power Consumption        | 28 W                      |
| Mechanical and Housing   |                           |
| Housing Color            | Aluminum                  |

| Approval and Application        |                                      |
|---------------------------------|--------------------------------------|
| Ingress protection code         | IP20 [Finger-protected]              |
| Protection class IEC            | Safety class I                       |
| Product Data                    |                                      |
| Order product name              | TCS640 C 2xTL5-28W HFP AC-MLO FU ALU |
| Full product name               | TCS640 C 2xTL5-28W HFP AC-MLO FU ALU |
| Full product code               | 911401015580                         |
| Order code                      | 911401015580                         |
| Material Nr. (12NC)             | 911401015580                         |
| Numerator - Quantity Per Pack   | 1                                    |
| Numerator - Packs per outer box | 1                                    |

## Arano TCS640 C

### Dimensional drawing

