



# Optivision MVP507 C

## MVP507 CMHN-LA2000W/842 380-415V MB

MASTER MHN-LA, 2000 W, Medium beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

### Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Gear	CONV [Conventional]

  

Light Technical	
Number of light sources	1
Light source color	842 neutral white
Optic type outdoor	Medium beam

  

Operating and Electrical	
Input Voltage	380 to 415 V
Line Frequency	50 Hz
Power Consumption	2,000 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

  

Product Data	
Order product name	MVP507 CMHN-LA2000W/842 380-415V MB
Full product name	MVP507 CMHN-LA2000W/842 380-415V MB
Full product code	911401042080
Order code	911401042080
Material Nr. (12NC)	911401042080
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Optivision MVP507 C

## Dimensional drawing

