



# Optivision MVP507 C

## MVP507 CMHN-LA1000W/842 220-240V WB

MASTER MHN-LA, 1000 W, Wide beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

### Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Light source color	842 neutral white
Optic type outdoor	Wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Power Consumption	1,000 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MVP507 CMHN-LA1000W/842 220-240V WB
Full product name	MVP507 CMHN-LA1000W/842 220-240V WB
Full product code	911401042380
Order code	911401042380
Material Nr. (12NC)	911401042380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Optivision MVP507 C

### Dimensional drawing

