



# ConTempo 150-250-350

## RVP350 HPI-T400W K IC 240V-50Hz A SP

MASTER HPI-T Plus, 400 W, Asymmetrical

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

### Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Cap-Base	E40 [E40]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Asymmetrical
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	400 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	RVP350 HPI-T400W K IC 240V-50Hz A SP
Full product name	RVP350 HPI-T400W K IC 240V-50Hz A SP
Full product code	911401057080
Local code description	RVP350HPI400TKA
Order code	911401057080
Material Nr. (12NC)	911401057080
Local order code	911401057080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828621179
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828621179

## ConTempo 150-250-350

### Dimensional drawing

