



# ConTempo 150-250-350

## RVP250 MHN-TD70W K IC 240V-50Hz A SP

MHN-TD, 70 W, Asymmetrical

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

### Product data

General Information	
Lamp family code	MHN-TD
Cap-Base	R7S [R7s]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Asymmetrical
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	70 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	RVP250 MHN-TD70W K IC 240V-50Hz A SP
Full product name	RVP250 MHN-TD70W K IC 240V-50Hz A SP
Full product code	911401057480
Order code	911401057480
Material Nr. (12NC)	911401057480
Local order code	911401057480
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828621063
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828621063

## ConTempo 150-250-350

### Dimensional drawing

