



Halolite

QVF135 HAL-TDS500W K 240V GR

Plusline Small (double-ended), 500 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

Product data

General Information	
Lamp family code	HAL-TDS [Plusline Small (double-ended)]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	500 W
Mechanical and Housing	
Housing Color	Grey

Product Data	
Order product name	QVF135 HAL-TDS500W K 240V GR
Full product name	QVF135 HAL-TDS500W K 240V GR
Full product code	692382868135799
Order code	911401062180
Material Nr. (12NC)	911401062180
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828681357
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828691783

Dimensional drawing

