



Halolite

QVF137 HAL-TDL1000W K 240V GR

Plusline Large (double-ended), 1000 W

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

Product data

General Information	
Lamp family code	HAL-TDL [Plusline Large (double-ended)]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	1,000 W
Mechanical and Housing	
Housing Color	Grey

Product Data	
Order product name	QVF137 HAL-TDL1000W K 240V GR
Full product name	QVF137 HAL-TDL1000W K 240V GR
Full product code	911401062280
Order code	911401062280
Material Nr. (12NC)	911401062280
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828681364
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828691790

Dimensional drawing

