



VerseBay HPK518

HPK518 1xHPI-P250W-BU IC 220V-50Hz

1, MASTER HPI Plus, 250 W, 220 V, 50 Hz

Reliable, effective lighting in the industrial workplace is a crucial factor influencing productivity, safety and staff well-being. The VerseBay high-bay luminaire clearly embodies such lighting requirements. Its solid, quality construction and reliable performance excels even in the toughest working environments. Its specially designed beam regulator allows light distribution to be optimally set for a broad range of work areas using just a single reflector. VerseBay also embodies extraordinary features that dramatically eases installation and maintenance. An external waterproof connector makes installation faster than ever while its tool-less lamp replacement is quick and hassle-free. So whatever your high-bay lighting requirements – industrial areas, logistics centers or public spaces – VerseBay offers a host of innovative features that can add new dimensions to versatility and ease of installation.

Product data

| General Information | | Approval and Application | |
|--------------------------|-------------------------|---------------------------------|------------------------------------|
| Lamp family code | HPI-P [MASTER HPI Plus] | Protection class IEC | Safety class I |
| Gear | CONV [Conventional] | | |
| Light Technical | | Product Data | |
| Number of light sources | 1 | Order product name | HPK518 1xHPI-P250W-BU IC 220V-50Hz |
| | | Full product name | HPK518 1xHPI-P250W-BU IC 220V-50Hz |
| | | Full product code | 911401089280 |
| | | Order code | 911401089280 |
| Operating and Electrical | | Material Nr. (12NC) | 911401089280 |
| Input Voltage | 220 V | Numerator - Quantity Per Pack | 1 |
| Line Frequency | 50 Hz | Numerator - Packs per outer box | 2 |
| Power Consumption | 250 W | | |

Dimensional drawing

