



VerseBay HPK518

HPK518 1xHPI-P400W-BUS IC 220V-50Hz

1, MASTER HPI Plus, 400 W, 220 V, 50 Hz

Reliable, effective lighting in the industrial workplace is a crucial factor influencing productivity, safety and staff well-being. The VerseBay high-bay luminaire clearly embodies such lighting requirements. Its solid, quality construction and reliable performance excels even in the toughest working environments. Its specially designed beam regulator allows light distribution to be optimally set for a broad range of work areas using just a single reflector. VerseBay also embodies extraordinary features that dramatically eases installation and maintenance. An external waterproof connector makes installation faster than ever while its tool-less lamp replacement is quick and hassle-free. So whatever your high-bay lighting requirements – industrial areas, logistics centers or public spaces – VerseBay offers a host of innovative features that can add new dimensions to versatility and ease of installation.

Product data

General Information	
Lamp family code	HPI-P [MASTER HPI Plus]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	400 W

Approval and Application	
Protection class IEC	Safety class I
Product Data	
Order product name	HPK518 1xHPI-P400W-BUS IC 220V-50Hz
Full product name	HPK518 1xHPI-P400W-BUS IC 220V-50Hz
Full product code	911401089380
Order code	911401089380
Material Nr. (12NC)	911401089380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

