



# EnduraBay HPK138/238

## HPK138 1xHPI-P250W-BU IC 220 50

1, MASTER HPI Plus, 250 W, 220 V, 50 Hz

HPK238's attractive and unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. Its robust, dependable construction along with its ease of installation and maintenance truly make this highbay luminaire a durable, yet appealing solution. EnduraBay LX HPK138. Elegance and efficiency were the themes driving the design of EnduraBay LX. Its attractive yet unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. What's more, it is easy on your budget. EnduraBay LX truly offers you peace of mind in your highbay installation. This robust luminaire makes it an impressive light source, as does its attractive minimalist design. The most striking feature of this high-bay luminaire is its four "shields" on the upper part of the housing, giving any lighting installation a distinctive elegance.

### Product data

General Information	
Lamp family code	HPI-P [MASTER HPI Plus]
Cap-Base	E40 [E40]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	220 V

Line Frequency	50 Hz
Power Consumption	250 W
Approval and Application	
Protection class IEC	Safety class I
Product Data	
Order product name	HPK138 1xHPI-P250W-BU IC 220 50
Full product name	HPK138 1xHPI-P250W-BU IC 220 50
Full product code	692382863066900

EnduraBay HPK138/238

Order code	911401092080
Material Nr. (12NC)	911401092080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828630669

Numerator - Packs per outer box	1
EAN/UPC - Case	6923828630669

Dimensional drawing

